



## 573EB

Product no.: 573EB

Distance cutter with variable cutting length from 0 mm to 5 mm/  
0 to .197 Inch




Special tool steel



ESD-safe



Variable cutting length (= V)



source images

### The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem distance cutters are available with fixed and variable cutting lengths. With the distance cutters wires can be cut to the correct length. They are also suitable to fix components. The tips are polished as to prevent board damage.

## THE PERFECT CUT

Strong, sharp and precise - every time

- + 1 Million Movements**  
Magic Spring™ design enables maximum durability with constant spring force movements
- + Quality**  
Uncompromising Swiss quality created to be strong, durable and sharp
- + Precision**  
Experience precise cuts from the high-precision screw joint that enables a smooth action with no jaw overlap
- + Strong and Sharp**  
Hand-crafted cutting edges for superior strength and sharpness
- + Comfort, Security and Grip**  
Ergonomically-shaped handles provide superior comfort and fatigue-free handling with Maximum Opening Stop Technology
- ESD Safe**  
Made from ESD-safe material to prevent damage to sensitive components

Weller Erem

Swiss Made

weller-tools.com





### Technical Data

|                                              |       |
|----------------------------------------------|-------|
| Length mm                                    | 125   |
| Length of cutting edges mm                   | 4     |
| Head width mm                                | 11    |
| Head thickness mm                            | ---   |
| Head length mm                               | 29    |
| Max. cutting capability – hard wire mm       | ---   |
| Weight in oz                                 | 2.469 |
| Length of cutting edges Inches               | 0.157 |
| Head width Inches                            | 0.433 |
| Head thickness Inches                        | ---   |
| Head length Inches                           | 1.142 |
| ESD-safe                                     | on    |
| Cut                                          | Flush |
| Max. cutting capability – medium hardness mm | ---   |
| Max. cutting capability – copper wire mm     | Ø 0.8 |
| Length inches                                | 4.921 |
| Weight in g                                  | 70    |
| Erem applications                            | ---   |