

USB Type-C™ to HDMI Cable (DP Alt Mode) 8K 60 Hz with HDR function 2 m red

Description

This cable by Delock enables the connection of an HDMI monitor to a PC or laptop with USB-C™ or Thunderbolt™ 3 port, such as a MacBook or a Chromebook. The interface has to support the DisplayPort Alternate Mode.



Item no. 80096

EAN: 4043619800964

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB Type-C™ male
 - 1 x HDMI male
- Chipset: Synaptics VMM7100
- High Speed HDMI with Ethernet (HEC) specification
- Signal direction: USB Type-C™ input > HDMI output
- Contacts gold-plated
- Resolution up to:
 - 7680 x 4320 @ 60 Hz
 - 3840 x 2160 @ 144 Hz
 - (depending on the system and the connected hardware)
- Transmission of audio and video signals
- Supports 3D displays
- Supports HDR10
- Supports HDCP 1.4 and 2.3
- Plug & Play
- Housing material: aluminium
- Length incl. connectors: ca. 2 m
- Colour: black / red

System requirements

- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or
- PC or laptop with a free Thunderbolt™ 3 port

Package content

- USB-C™ to HDMI cable

Images



General

Specification:	HDCP 1.4 HDCP 2.3 HDMI 2.1 HDR10 USB Type-C™
----------------	--

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x HDMI male

Technical characteristics

Chipset:	Synaptics VMM7100
Maximum screen resolution:	7680 x 4320 @ 60 Hz 3840 x 2160 @ 144 Hz

Physical characteristics

Housing material:	Aluminium
Pin finishing:	gold-plated
Length:	2 m
Colour:	black / red

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de