

DisplayPort 1.2 cable 4K 60 Hz 5 m without latch

Description

This DisplayPort cable by Delock can be used to connect devices with DisplayPort interface, e.g. displays, projectors or TVs, to a PC or laptop. The triple shielded cable supports a resolution of up to Ultra HD (4K @ 60 Hz) and is downwards compatible to Full-HD 1080p.

Slim plug

Thanks to the missing latch, the plugs are a bit slimmer than standard DisplayPort plugs, so several ports can be used simultaneously. In addition, the plugs can be removed more easily from hard-to-reach DisplayPort ports, e.g. on the rear side of a monitor.



Item no. 85912

EAN: 4043619859122

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x DisplayPort male >
 - 1 x DisplayPort male
- DisplayPort 1.2 specification
- Pin 20 not connected
- Cable gauge: 30 AWG
- Cable diameter: ca. 5.7 mm
- Copper conductor
- Triple shielded cable
- Contacts gold-plated
- Transmission of audio and video signals
- Data transfer rate up to 21.6 Gbps
- Resolution up to 3840 x 2160 @ 60 Hz
(depending on the system and the connected hardware)
- Supports HDR
- Supports HDCP 1.4 and 2.2
- Supports colour sampling in 4:4:4, 4:2:2 and 4:2:0 format
- Colour: black
- Length incl. connectors: ca. 5 m

System requirements

- A free DisplayPort interface

Package content

- DisplayPort cable

Images



General

Specification:	DisplayPort 1.2 HDCP 1.4 HDCP 2.2 HDR
Style:	both sides identical

Interface

Connector 1:	1 x DisplayPort male
Connector 2:	1 x DisplayPort male

Technical characteristics

Data transfer rate:	21.6 Gbps
Maximum screen resolution:	3840 x 2160 @ 60 Hz

Physical characteristics

Pin finishing:	gold-plated
Conductor material:	copper
Cable gauge:	30 AWG
Shielding:	triple
Length:	5 m
Colour:	black
Cable diameter:	5.7 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de