

# UTP Cat6 Patch cord, 1.5 m, green

PP6U-1.5M/G



## Features

- CAT6 stranded unshielded (UTP) patch cord, 8P8C
- Snagless boots

## Specifications

Category: category 6  
 Type: UTP (unshielded)  
 Frequency bandwidth: Max. 250 MHz  
 Compliance with ANSI / TIA / EIA-568B standards  
 Conductor: AWG 26 (7 x 0.15 mm wire), CCA  
 Conductor insulation: HDPE 0.85 mm  
 Shielding: n/a  
 LDPE filler: yes  
 Polyester tape: n/a  
 Drain wire: n/a  
 Jacket material: PVC  
 Jacket braiding: n/a  
 Jacket outer diameter: 6.2 mm  
 Length: conform item description  
 Color: conform item description

## Packaging

|                                |                |
|--------------------------------|----------------|
| Q'ty in crtn, pcs              | 200            |
| Crtn volume, CUM               | 0.036          |
| Crtn weight, kgs               | 6.94           |
| Individual package size LxWxH: | 180x130x5 mm   |
| Carton size LxWxH:             | 400x300x300 mm |
| Country of origin              | CN             |
| Barcode                        | 8716309126991  |
| Customs code                   | 8544421000     |

## Certificates

