

# Cable USB 2.0 Type-A female > USB 2.0 Type-A female panel-mount 0.5 m

## Description

This cable by Delock can be used to extend an USB connection and to connect various devices. The female port can be attached with two screws, e.g. to a slot bracket, a cable duct or an enclosure with the corresponding opening. In this way, it is possible to install a USB connector in an easily accessible position.



0.5 m

**Item no. 85459**

EAN: 4043619854592

Country of origin: China

Package: Zip poly bag

## Technical details

- Connectors:
  - 1 x USB 2.0 Type-A female >
  - 1 x USB 2.0 Type-A female with nuts for installation
- Screw type: #4-40 UNC
- Mounting hole: ca. 15 x 8 mm, screw hole pitch ca. 30 mm
- Cable gauge:
  - 28 AWG data line
  - 24 AWG power line
- Cable diameter: ca. 4.5 mm
- Gold-plated connectors
- Data transfer rate up to 480 Mb/s
- Colour: black
- Length incl. connectors: ca. 50 cm

## System requirements

- A free USB interface

## Package content

- USB panel-mount cable
- 2 screws

---

## Images



## General

Specification:	USB 2.0
Style:	both sides identical

## Interface

Connector 1:	1 x USB 2.0 Type-A female
Connector 2:	1 x USB 2.0 Type-A female

## Technical characteristics

Data transfer rate:	480 Mbps
---------------------	----------

## Physical characteristics

Pin finishing:	gold-plated
Cable gauge:	28 AWG data line 24 AWG power line
Screw distance:	30 mm
Screw type:	#4-40 UNC
Length:	50 cm
Colour:	black

## Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de