



Qoltec Certified Wireless Smoke Detector with Battery | Sensor life: 10 years | Battery life: 10 years | Alarm: 85dB | LED

Product code: 52653

Ensure the safety of your home, office, or flat with a modern, certified wireless smoke detector that combines reliability with long service life and simple installation. The device is equipped with an efficient sensor with a service life of up to 10 years and a loud 85 dB audible alarm that effectively warns household members of danger.

ENSURE YOUR SAFETY AND THAT OF YOUR LOVED ONES



Immediate danger warning – dual warning system

It is worth taking care of safety today and equipping your house, flat or garage with a smoke detector. **The device reacts instantly – in the event of danger, it activates a loud 85dB (decibel) audible alarm and a visual alarm in the form of a red LED light.** Thanks to the dual warning system, you can be sure that the alarm signal will reach all household members in time, even at night when the danger is particularly high.

CERTIFIED QOLTEC SMOKE DETECTOR – RELIABLE PROTECTION



Key product features

- **Optical sensor** – high accuracy and durability for up to 10 years
- **Self-diagnostics** – constant monitoring of the sensor and internal circuits
- **Optical sensor** – high smoke detection accuracy and service life of up to 10 years
- **Fault indication** – LED warns of malfunction
- **TEST button** – easy performance check
- LED indicating the operating status of the device
- Immediate warning of danger – **85 dB audible alarm + LED light alarm**
- **Certified compliance with EN 14604:2005/AC:2008 standards**

CONTROL AND RELIABILITY – WHENEVER YOU NEED IT



Simple installation in a few steps,

You do not need any special tools or professional assistance.

Installation is quick, intuitive and can be done by yourself. The sensor can be installed quickly and intuitively without interfering with the gas or electrical systems.

- Screw or glue the mounting plate to the wall in the appropriate place (e.g. in the kitchen, boiler room or garage) using the tape provided.
- Place the device on the hooks and lock it in the guides.

You can test the operation yourself using the TEST button.

The device is equipped with a TEST button, which allows you to easily check its performance:

- With one click, you can activate a test alarm,
- You can ensure that the sound and light are functioning correctly,
- You can be confident that the sensor will respond in the event of a real threat.

CONFIDENCE CONFIRMED BY A WARRANTY



The product is covered by a 24-month warranty.

Do you care about the high quality of the product you are buying? Our solutions will meet your expectations. Each of the barcode readers we offer is covered by a **24-month warranty** valid from the date of purchase.

TECHNICAL DATA

Producer	Qoltec
Type	Electrochemical and optical sensor (10-year lifespan)
Alarm sound level	85dB
Technical model	ZR150SL
Range	~3m
Power supply	1 x 3V DC CR123A 1600 mAh battery (non-replaceable)
Working time	Ten years after activation, the sensor will remind you that it needs to be replaced
Battery life	10 years
Power consumption	50mA
Built-in battery	Yes
Display	No
Installation	Using screws or 3M adhesive tape
Application	Flats, detached houses, motorhomes, garages, basements, boiler rooms
OTHER PARAMETERS	
Colour	White
Material	ABS
Operating temperature	-10 55
Dimensions (D/L x W x H)	76 x 76 x 25 mm
Package contents	1 x Sensor 1 x User manual 1 x Warranty card 1 x Screws and double-sided tape
Package	Box
Package depth / length [mm]	87
Package width [mm]	80
Package height [mm]	35
Net weight [kg]	0.099
Gross weight [kg]	0.111
Certificate	CE, fire safety certificate EN 14604:2005+AC:2008
Warranty	24 month
EAN code	5901878526539