

# Product Datasheet

Item No.: 12236

PRODUCT NAME

## Garden extension reel 25 m H05RR-F 3G1,5 IP44



- Reel body made from robust, shatter-proof special plastic with cable reel
- With stable, shock-absorbing and galvanized single-foot frame with parking brake
- Frame with ergonomically shaped handle and cable guide
- With built-in thermal circuit breaker
- Connector for shock-proof plugs with lockable safety cover
- With 1.5 m power cord with shock-proof plug
- Cable in red signal color
- IP44: protected against foreign bodies and splash-proof
- 230 V, 16 A, max. 3,500 W

Reference image

### Technical data

EAN	4011160122361
Weight [kg]	4.5
Dimensions	20x32,5x22,5 cm
Main color	green
Category	Cable reels
Subcategory	Extension reels for Outdoor Use
Cable type	H05RR-F
Cross section [mm <sup>2</sup> ]	3G1,5
Cable color	red
Cable length [m]	25
Rated voltage [V]	230
Rated current [A]	16
Maximum power	3500 W
Brake	Yes
Drum diameter	230 mmØ
Metal frame	Yes
Thermal fuse	1P
IP protection	IP44
Input	Shock-proof plug 230 V, 16 A, IP44 with 25 m H05RR-F 3G1,5
Output	1x shock-proof connector with red cover 230 V, 16 A, IP44
Total number of sockets	1
Number of Type F sockets (230 V)	1
Number of cores	3

Your partner for professional lighting and electrical products.