

19" Fiber Optic HD (High Density) Patch Panel 1U black

Description

This patch panel by Delock can be mounted in a 19" rack. It can accommodate up to four HD cassettes or fiber optic adapter panels and two splice cassettes.

For the installation of fiber optic adapter panels

The adapter panels can be added, moved or changed individually. A wide selection of matching adapter panels with pre-assembled fiber optic couplers is available as accessory.

Rear cable entry

The fiber optic cables can easily be passed through via four cable entry holes in the rear part of the patch panel. The cover can be removed to allow easy cable entry.

Optional routing panel for optimal cable management

A suitable routing panel is available as an accessory, it can be easily mounted on the patch panel and enables neat cable routing. With the help of the patch panel, cables can be prevented from damage, e.g. by twisting and bending.



Item no. 66924

EAN: 4043619669240

Country of origin: China

Package: Box

Technical details

- For mounting in 19" racks, 1U
- For HD cassettes or fiber optic adapter panels
- Up to 144 fibres
- 4 rear cable entries
- Removable cover
- Housing colour: black
- Dimensions (LxWxH): ca. 482.6 x 220.0 x 43.6 mm

System requirements

- HD cassettes or fiber optic adapter panels

Package content

- 19" fiber optic HD (High Density) patch panel
- 4 x screws
- 4 x caged nut

Images



application example



application example



application example



application example



General

Mounting type:	19 in
----------------	-------

Physical characteristics

Housing colour:	black
Material:	metal
Length:	482.6 mm
Width:	220.0 mm
Height:	43.6 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

