

UTP Cat6 Patch cord, 5 m, yellow

PP6U-5M/Y

- Perfect connection
- Gold plated contacts



Features

- CAT6 stranded unshielded (UTP) patch cord, 8P8C
- Snagless boots

Specifications

Patch cord category 6 UTP (unshielded)
 Length: according to the item
 Structure: AWG 26 (7 x 0.15 mm wire), CCA
 HDPE insulation of the wire: 0.85 mm
 With LDPE filler
 With polyester tape: not used
 With aluminum foil: not used
 Drain hose: not used
 PVC outer insulation: 6.2 mm
 Color: according to the item
 Operation up to 250 MHz

Packaging

Q'ty in crtn, pcs	50
Crtn volume, CUM	0.036
Crtn weight, kgs	6.27
Individual package size LxWxH:	190x150x35 mm
Carton size LxWxH:	400x300x300 mm
Country of origin	CN
Barcode	8716309093132
Customs code	8544421000

Certificates

