

Keystone Module USB 2.0 Type-A panel mount female 45° angled to Type-A female with 30 cm cable black

Description

This module by Delock can be used to extend e.g. a USB cable.

With mounting holder for installation

The adapter can be installed e.g. on a panel, in a housing or switch cabinet.

With angled connection

The angled connection enables space-saving installation in tight spaces and hard to reach places in equipment or in cable ducts.



Item no. 67152

EAN: 4043619671526

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A female
 - 1 x USB 2.0 Type-A female 45° angled for installation
- Data transfer rate up to 480 Mbps
- Cable gauge:
 - 28 AWG data line
 - 24 AWG power line
- Current: max. 0.8 A
- Electrical power: max. 4 watt
- With mounting holder for installation
- Holder (WxH): ca. 40 x 18 mm
- Mounting hole diameter: ca. 2.2 mm
- Pitch of screw hole: ca. 30 mm
- Screw connection #4-40 UNC
- Cable diameter: ca. 4.5 mm
- Housing material: PC + ABS
- Colour: black
- Cable length: ca. 30 cm

Package content

- USB cable
- 2 x screw

Images



General

Style:	both sides identical
--------	----------------------

Interface

Connector 1:	1 x USB 2.0 Type-A female
Connector 2:	1 x USB 2.0 Type-A female 45° angled for installation

Physical characteristics

Cable gauge:	28 AWG data line 24 AWG power line
Material:	PC + ABS
Length:	30 cm
Colour:	black
Cable diameter:	4.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

