


HANGZHOU ONTECK INDUSTRIES LIMITED

REV	DESCRIPTION	DATE
A	IPEX-RP-SMA	2025-7-16



Electrical Performance

- 1 Impedance 50 ohms
- 2 Frequency Range: 0-5GHz
- 3 V.S.W.R: ≤ 2.0
- 4 Operating Voltage: 300Vrms Max.
- 5 Insulator Resistance: 10 Megohms Min.
- 6 Operating Temperature: -40°C~+90°C
- 7 Open and Short Test

PART NO.	IPEX-RP-SMA-500		
DTAWN BY	Kevin	DRAWTNG NO.	
CHECKED BY		SCALE	
APPROVED BY		UNIT	mm
SORTING NO.		PAGE	1