

ISM 433 MHz Antenna SMA plug -0.5 dBi omnidirectional flexible black

Description

This antenna by Delock allows the usage of the 433 MHz band indoors.



Item no. 12712

EAN: 4043619127122

Country of origin: China

Package: Zip poly bag

Technical details

- Connector: 1 x SMA plug
- Frequency range: 433 MHz
- Antenna gain: -0.5 dBi
- Polarisation: linear, vertical
- Impedance: 50 Ohm
- VSWR: 1.4
- Operating temperature: -40 °C ~ 85 °C
- Antenna length: ca. 4.73 cm
- Diameter: ca. 8.5 mm

System requirements

- Device with a free SMA connector

Package content

- Antenna

Images



General

Suitable for indoor:	yes
----------------------	-----

Interface

Connector:	1 x SMA plug
------------	--------------

Technical characteristics

Frequency range:	433 MHz
Antenna gain:	-0.5 dBi
Impedance:	50 Ω
Transmission power:	25 W
VSWR:	1.4

Physical characteristics

Housing material:	ABS
Diameter:	8.5 mm
Length:	4.73 cm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

