

## CONFIDENCE CONFIRMED BY A WARRANTY

The product is covered by a 24-month warranty

Do you value high-quality products? Our solutions will meet your expectations. Each of our chargers comes with a **24-month warranty from the date of purchase**.

## TECHNICAL DATA

Producer	Qoltec
Type	Rechargeable Battery Charger
Battery capacity	AA : 1800mA AAA : 900mA
Input	5V/2A
DC output	1.2VDC
Battery charging current	AA : 500mA 15%, AAA : 500mA 15%
Number of batteries	Charger for up to 4 Rechargeable Batteries
Compatibility	Ni-MH, Ni-Cd, R6/AA, R03/AAA
Display	LCD
Power cable	USB/USB-C with length ~ 0.55m
Protection	Overcurrent Overvoltage
Additional information	Can be recharged via USB charger, power bank, laptop or car USB socket To initiate the charging process, insert the batteries according to their polarity
OTHER PARAMETERS	
Colour	White
Material	ABS + plastic
Operating temperature	0°C ~ +35°C
Storage temperature	-25°C do +60°C
Storage humidity	85%
Dimensions (D/L x W x H)	25 x 85 x 65 mm
Package	Box
Package contents	1 x Battery charger 1 x USB-C cable 1 x User manual
Package depth / length [mm]	30
Package width [mm]	70
Package height [mm]	115
Net weight [kg]	0.080
Gross weight [kg]	0.091
Warranty	24 month
EAN code	5901878508481