



## BETA 584/C31

Assortment of 1 torque screwdriver, 8 hi-torque hexagon nut spinners, 20 bits and 2



### Certifications and Standards



## Features

Complete and versatile assortment for precise and secure tightening from 1 to 5 Nm, thanks to the dial indication torque screwdrivers and accessories.

### ORGANISATION AND PROTECTION

All contents are perfectly organised inside the soft EVA tray and protected by the robust metal case. Your tools are protected, easy to find and safe to transport everywhere.

### SAFETY

The slip system prevents the set torque being exceeded; when it is reached, the screwdriver slides and automatically reloads for the next tightening operation.

### SIMPLE ADJUSTMENT

The clearly readable double scale allows the torque to be set easily and accurately.

### ERGONOMICS AND CONTROL

The large, ergonomically designed handle ensures comfort and maximum grip during every operation.



### COMPLETENESS

The presence of both bits and sockets allows precision tightening of different types of screws and nuts.



### VERSATILE

The 1/4" female hexagon socket allows the use of bits and sockets making the screwdriver useful for a variety of jobs.



### OPERATING PANEL

1/4" female square drive on the bottom of the handle allows the use of a "T" wrench to exert less force.

Certifications and Standards



- 584/5: n. 1 - 5 Nm
- 900: n. 1/4" hexagon sockets 4-5-5,5-6-7-8-9-10 mm
- 860LP: n. bits for slotted head screws, coloured 0,6x4,5 - 1x5,5 - 1,2x6,5 mm
- 860PH: n. bits for cross head Phillips® screws, coloured PH1 - PH2 (x2) - PH3
- 860PE: n. hexagon bits for power drivers, coloured 2-2,5-3-4-5 mm
- 860TX: n. bits for Torx® head screws, coloured T9-T10-T15-T20-T25-T27-T30-T40
- 882P/80: n. magnetic bit holder extension bar 80 mm
- 892/O: n. adaptors for drivers 1/4 B 1/4

Coded items

|  | Art.    |
|-----------------------------------------------------------------------------------|---------|
| 005840931                                                                         | 584/C31 |

Scan the QR Code to access the web tab  
Specs, media and documentation in one click.

