

USB 2.0 Cable USB Type-C™ male to male with extended bend protection 60 W 1 m

Description

This USB cable by Delock enables the connection between a device with a USB Type-C™ connector and a PC or a laptop equipped with a free USB Type-C™ port. Supporting the USB Power Delivery standard, connected devices can be powered up to 60 W (20 V / 3 A).

Quality and performance

Optically it convinces with its fine textile shielding and with its connector in metal housing. The high cable gauge of the power line with 22 AWG also supports a stable power supply of up to 3 A.



Item no. 81124

EAN: 4043619811243

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
1 x USB Type-C™ male
1 x USB Type-C™ male
- Cable gauge:
30 AWG data line
22 AWG power line
- USB Power Delivery (USB PD 3.0) support up to 60 watt (20 V / 3 A)
- Cable diameter: ca. 4 mm
- Data transfer rate up to 480 Mbps
- Cable with textile shielding
- Connector with metal housing
- Colour: black
- Length: ca. 1 m

Package content

- USB 2.0 cable

Images



General

Specification:	USB 2.0 USB Type-C™
Style:	both sides identical

Interface

Connector 1:	1 x USB 2.0 Type-C™ male
Connector 2:	1 x USB 2.0 Type-C™ male

Technical characteristics

Data transfer rate:	480 Mbps
Maximum current:	3 A

Physical characteristics

Cable gauge:	30 AWG data line 22 AWG power line
Length:	1 m
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de