

USB Type-C™ Adapter to HDMI (DP Alt Mode) 8K with HDR function aluminium

Description

This adapter by Delock is suitable for the connection of a HDMI monitor in **8K Ultra HD** (7680 x 4320 @ 30 Hz) resolution to a computer with **USB-C™** interface and DisplayPort alternate mode support. Thus, the adapter can be connected to different laptops like MacBook, Chromebook and similar. In addition, the adapter can also be operated on a Thunderbolt™ 3 interface.



Quality and stability

In addition, the cable convinces with various properties that support long-term use. It is equipped with noble **aluminium housings**, a **textile shielding** as well as **strain relief elements** at both connector ends.

Item no. 64229

EAN: 4043619642298

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
1 x USB Type-C™ male
1 x HDMI female
- Chipset: VIA VL103 + Synaptics VMM6100
- DisplayPort 1.4 specification
- Resolution up to 7680 x 4320 @ 30 Hz (depending on the system and the connected hardware)
- Transmission of audio and video signals
- Supports 3D displays
- Supports HDR10
- Supports HDCP 1.4 and 2.3
- USB bus powered
- Plug & Play
- Cable with textile shielding
- Housing material: aluminium
- Cable length without connectors: ca. 20 cm
- Colour: grey

System requirements

- Android 10.0 or above
- Chrome OS 91.0 or above

- Linux Kernel 5.11 or above
- Mac OS 11.2.3 or above
- Windows 8.1/8.1-64/10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- Surface Pro 7
- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or
- PC or laptop with a free Thunderbolt™ 3 port

Package content

- USB-C™ to HDMI adapter

Images



General

Function:	Plug & Play
Specification:	HDCP 1.4 HDCP 2.3 HDR10
Supported operating system:	Surface Pro 7 Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Android 10.0 or above iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Mac OS 11.2.3 or above Windows 11 Linux Kernel 5.11 or above Chrome OS 91.0 or above

Interface

Output:	1 x HDMI-A female
Input:	1 x USB Type-C™ male

Technical characteristics

Chipset:	VIA VL103 Synaptics VMM6100
Maximum screen resolution:	7680 x 4320 @ 30 Hz
Signal transmission:	video audio

Physical characteristics

Housing material:	Aluminium
Cable length:	20 cm
Colour:	grey

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de