

Han CGM-P-EXi M40 D 22...32mm



Part number	19 00 000 7109
Specification	Han CGM-P-EXi M40 D 22...32mm
HARTING eCatalogue	https://b2b.harting.com/19000007109

Identification

Category	Accessories
Series of hoods/housings	Han [®] CGM-Ex i
Type of accessory	Cable gland

Version

Field of application	Intrinsically safe electric circuits
----------------------	--------------------------------------

Technical characteristics

Limiting temperature	-40 ... +100 °C
Tightening torque	≤10 Nm (depending on the cable and the seal insert used)
Wrench size	53
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M40
Clamping range	22 ... 32 mm
Width across corners	58.8 mm

Material properties

Material (seal)	NBR
Material (cable glands)	Polyamide (PA)
Colour (accessories)	RAL 7032 (pebble grey) RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant



Pushing Performance

Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	68.8 g
Country of origin	Germany
European customs tariff number	39269097
eCl@ss	27144432 Screwed cable gland (electr.)