

# Adapter DVI male to DisplayPort 1.2 female black 4K with HDR function 50 cm

## Description

This adapter by Delock can be used to connect e.g. a DisplayPort monitor to a free DVI interface of the system.



**Item no. 63189**

EAN: 4043619631896

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x DVI 24+1 male with screws
  - 1 x USB Type-A male (power supply)
  - 1 x DisplayPort female
- Chipset: STDP2600
- DVI-D (Single Link), VGA not wired
- DisplayPort 1.2 specification
- Signal direction: DVI input > DisplayPort output
- Resolution up to 3840 x 2160 @ 30 Hz  
(depending on the system and the connected hardware)
- Transmission of audio and video signals
- Supports HDR
- Supports HDCP 1.4
- Plug & Play
- Colour: black
- Cable length without connectors: ca. 50 cm
- OS independent, no driver installation necessary

## System requirements

- A free DVI 24+1 female port

- A free USB Type-A female port
- Monitor with a free DisplayPort interface
- DisplayPort connection cables

---

## Package content

- DVI to DisplayPort Adapter

---

## Images



## General

Function:	Plug & Play
Specification:	DVI-D (Single Link) DisplayPort 1.2 HDCP 1.4
Supported operating system:	OS independent, no driver installation necessary

## Interface

Output:	1 x DisplayPort female
Input:	1 x DVI 24+1 male with screws 1 x USB Type-A male (power supply)

## Technical characteristics

Chipset:	Kinetic STDP2600
Maximum screen resolution:	3840 x 2160 @ 30 Hz
Signal transmission:	video audio

## Physical characteristics

Cable length:	50 cm
Colour:	black

## Manufacturer information

---

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de