



Click [here](#) for the 3D model.

Dimensions	
D	25mm MAX
H	19mm MAX
LL	8mm +/-2mm
S	10mm
S1	19mm
Wire Size	0.9mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	500
Typical Component Weight	19.3 g

General Information	
Series	SC
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Mn-Zn Ferrite

Specifications	
Voltage AC	250 VAC
Inductance	1 mH (100 kHz)
Current	6 A
Temperature Range	-40/+120°C
DC Resistance	27 mOhms