

# 19" Fibre Patch Panel 24 port LC Duplex beige

## Description

This patch panel by Delock can be mounted in a 19" rack. The jacks on the front and rear of the panel provide convenient connections for fibre patch cable.



**Item no. 43388**

EAN: 4043619433889

Country of origin: China

Package: White Box

## Technical details

- Connectors:
  - 24 x LC Duplex female >
  - 24 x LC Duplex female
- Colour: beige
- For 48 OM2 Multi-mode fibers
- Zirconia ceramic ferrule with protection cap
- For mounting in 19" racks, 1U
- Removable strain relief
- Housing colour: black
- Dimensions (LxWxH): ca. 482.6 x 150.0 x 43.6 mm

## Package content

- 19" patch panel

## General

|                |                      |
|----------------|----------------------|
| Unit height:   | 1                    |
| Mounting type: | 19 in                |
| Style:         | both sides identical |

## Physical characteristics

|                 |          |
|-----------------|----------|
| Housing colour: | black    |
| Depth:          | 150 mm   |
| Width:          | 482.6 mm |
| Height:         | 43.6 mm  |

## Manufacturer information

|             |                   |
|-------------|-------------------|
| Street      | Beeskowdamm 13/15 |
| Postal code | 14167             |
| City        | Berlin            |
| Country     | Deutschland       |
| E-Mail      | info@delock.de    |
| Website     | www.delock.de     |

