

Product designation	Electronic current transformers for EASY BRANCH system				
Product type designation	EXS3125				
Type	Three-phase				
Current inputs					
Rated current (Ie)	A	125			
Current					
IEC maximum (Imax)	A	125			
IEC rated (Iref-lb)	A	20			
IEC start (Ist)	mA	40			
Insulations					
Rated insulation voltage Ui IEC/EN	V	600			
Mechanical features					
Housing type	Polyamide				
Terminals type	RJ45				
Weight	g	180			
Ambient conditions					
Temperature					
Operating temperature	min	°C	-30		
	max	°C	+70		
Storage temperature	min	°C	-30		
	max	°C	+80		
Relative humidity	%	<80			
Maximum Pollution degree	2				
Overvoltage category	3				
Protection degree	IP20				
Certifications and compliance					
Compliance					
IEC/EN/BS 61000-6-2					
IEC/EN/BS 61000-6-4					
IEC/EN/BS 61010-1					
Certificates					
CE					
EAC					
UKCA					
ETIM classification					
ETIM 8.0	EC002475 - Current value transformer				