

**3200**

HSA DOUBLE SIDED TAPE



- Double sided acrylic tape with very high adhesive strength
- Specially designed for (heavy) trims, signs, strengtheners, etc.
- Good adhesion to metal, glass and most plastics
- Repositionable (15 min)

Art. No.	width	length	colour	Pack.	EAN code
HSA024	12 mm	2 m	black	20	8711347125005
HSA025	19 mm	2 m	black	20	8711347125029

Adhesive: acrylic

Carrier: acrylic foam

Maximum temperature: 93°C (up to 150°C for short periods)

Adhesive strength: 53 N/25 mm

Thickness: 1,10 mm

HPX

Frankrijkstraat 8 | 9140 Temse | Belgium

T 0032 3 710 19 19 | F 0032 3 711 34 64 | info@hpx.eu | www.hpx.eu

