

Product Datasheet

Item No.: 11611



PRODUCT NAME

6-way multi socket outlet 1,4 m H05VV-F 3G1,5 WH IP20



Reference image



- With PVC cable H05VV-F 3G1.5 and shock-proof angle plug
- Sockets rotated 45°, with increased touch protection
- 230 V, 16 A, max. 3,500 W

Technical data

EAN	4011160116117
Weight [kg]	0.39
Dimensions	7x4,5x35 cm
Main color	white
Category	House and garden
Subcategory	Multi socket outlets & multiplugs
Cable type	H05VV-F
Cross section [mm²]	3G1,5
Cable color	white
Cable length [m]	1.4
Rated voltage [V]	230
Rated current [A]	16
Maximum power	3500 W
IP protection	IP20
Input	Shock-proof angle plug 230 V, 16 A, IP20
Output	6x shock-proof connector 230 V, 16 A, IP20
Total number of sockets	6
Number of Type F sockets (230 V)	6

Your partner for professional lighting and electrical products.

