

TECHNICAL DATA

Producer	Qoltec
Power	300W
Input voltage	220 – 240 V
Output voltage	12V / 24V
Type of charging	6 step charging mode
Battery capacity	20Ah-300Ah
Charging time	Depending on battery capacity
Connector	Red + black crocodile type terminals
Cooling system	1 x Fan
Display	LCD
Protection	Reverse polarity protection Overvoltage protection Short-circuit protection Overcurrent protection Protection against overheating Low voltage protection
Protection against inverse polarity	Yes
Cable length	0.50m
Power cord length	1.18m
Functions	Battery repair function
Usage	Maintenance-free batteries: AGM GEL SLA WET Calcium
Additional information	With cable organizers
OTHER PARAMETERS	
Colour	Black
Material	Plastic
Operating temperature	-30°C ~ +50°C
Dimensions (D/L x W x H)	135 x 170 x 65 mm
Package	Box
Package contents	1 x Charger 1 x Warranty card 1 x Operating instructions
Package depth / length [mm]	110
Package width [mm]	220
Package height [mm]	195
Net weight [kg]	0.657
Gross weight [kg]	0.772
Certificate	CE
Warranty	24 month
EAN code	5901878525143