

Cable High Speed HDMI with Ethernet - HDMI-A male > HDMI-A male 4K 2.0 m

Description

The High Speed HDMI with Ethernet cable by Delock combines fast data transfer as well as audio- / video and Ethernet connection in one. It is used to connect DVD or Blu-ray devices to a TV or a monitor to a PC or a laptop. The cable also supports 4K Ultra HD resolutions, provided that all connected devices are compatible.



Item no. 82583

EAN: 4043619825837

Country of origin: China

Package: Retail Box

Technical details

- Connector:
 - 1 x High Speed HDMI-A 19 pin male >
 - 1 x High Speed HDMI-A 19 pin male
- High Speed HDMI with Ethernet (HEC) specification
- Cable gauge: 28 AWG
- Cable diameter: ca. 7.3 mm
- Twisted-pair cabling
- Copper conductor
- Gold-plated connector
- Transfer of audio and video signals
- Data transfer rate up to 10.2 Gb/s
- Resolution up to 3840 x 2160 @ 30 Hz (depending on the system and the connected hardware)
- 3D support up to 1080p in two video streams with each 60 pictures per second
- Up to 120 Hz refresh rate
- Contains the new Audio Return Channel (ARC)
- Uses new advanced colour space for presentation of digital pictures
- Supports Dolby® TrueHD and DTS-HD Master Audio™
- More lively and natural colours
- Colour: black
- Length without connector: ca. 2.0 m

System requirements

- A free HDMI interface

Package content

- HDMI cable

Images



General

Specification:	HDMI 1.4
Style:	both sides identical

Interface

Connector 1:	1 x HDMI-A male
Connector 2:	1 x HDMI-A male

Technical characteristics

Data transfer rate:	10.2 Gbps
Maximum screen resolution:	3840 x 2160 @ 30 Hz
Maximum refresh rate:	120 Hz

Physical characteristics

Pin finishing:	gold-plated
Conductor material:	copper
Cable gauge:	28 AWG
Length:	2 m
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de