

Product Datasheet

Item No.: 859250

PRODUCT NAME

Construction site armored cable, extension with 1-way socket outlet 50 m H07BQ-F 3G2,5 OG IP44 "F"



Reference image



- Approved for use on construction sites and in agricultural applications
- IP44: protected against foreign bodies and splash-proof
- Shock-proof plug and shock-proof connector with protective cap
- 230 V, 16 A
- "F"

Technical data

EAN	4059948000920
Weight [kg]	9.4
Dimensions	35x15x35 cm
Main color	orange
Category	Extensions
Subcategory	For use on construction sites
Cable type	H07BQ-F
Cross section [mm ²]	3G2,5
Cable color	orange
Cable length [m]	50
Rated voltage [V]	230
Rated current [A]	16
Maximum power	3500 W
IP protection	IP44
Input	Shock-proof plug 230 V, 16 A, IP44
Output	1x shock-proof connector with protective cap 230 V, 16 A, IP44 "F"
Total number of sockets	1
Number of Type E sockets (230 V)	1
Number of cores	3

Your partner for professional lighting and electrical products.