

Docking Station Dual USB Type-C™ with HDMI / USB 3.2 / SD / PD 3.0

Description

This docking station by Delock can be connected to a MacBook with two adjacent Thunderbolt™ 3 ports, e.g. the MacBook Pro. It is also possible to insert one of the two USB-C™ plugs into the housing, so that the docking station can also be connected to other devices such as a smartphone, tablet or laptop. One monitor with **4K 30 Hz** can be operated at the HDMI output port. One built-in **USB Type-C™ port** and two **USB Type-A ports** allows the use of peripherals.

USB Type-C™ pass-through

One of the two USB-C™ female ports is coupled to the insertable USB-C™ plug. This means that when it is extended (when used with a MacBook), the **USB-C™ female port (pass-through)** provides the full function of the USB-C™ interface. This port can transmit data at **10 Gbps**, charge the device (PD 3.0), or connect another monitor with a resolution of up to **4K 60 Hz**. In addition, as with **MST**, two additional monitors can be operated independently of each other (extended display).

If the docking station is only operated with one USB Type-C™ port, the USB-C™ (pass-through) female port has no function.

Integrated Card Reader

In addition, the docking station with integrated card reader expands mobile devices by an **SD** and a **Micro SD** slot via the USB Type-C™ connection.

USB Power Delivery (USB PD 3.0) support up to 100 watt

The docking station has a USB Type-C™ Power Delivery port to connect the power supply of the laptop or tablet to charge it. The docking station can also be used without a power supply.

Small sturdy helper

Due to its small dimensions and its **sturdy housing**, this Delock docking station is particularly suitable for travelling. It can simply be packed into the bag together with the laptop and used as needed.



Item no. 87752

EAN: 4043619877522

Country of origin: China

Package: Retail Box

Please Note

Only one additional external monitor can be connected to MacBook devices with M1, M2 and M3 chipset. MacBook devices with M1 Pro, M2 Pro, M3 Pro and M3 Max chipset can connect two or more additional external monitors. Further information is available at www.apple.com.

Technical details

- Connectors:
 - 2 x USB Type-C™ male
 - 1 x HDMI-A female
 - 2 x SuperSpeed USB (USB 3.2 Gen 1) Type-A female
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) USB Type-C™ female PD 2.0
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) USB Type-C™ female PD 3.0 (pass-through)
 - 1 x SD slot
 - 1 x Micro SD slot
 - Resolution:
 - HDMI up to 3840 x 2160 @ 30 Hz
 - USB-C™ DP Alt Mode up to 3840 x 2160 @ 60 Hz (pass-through)
(depending on the system and the connected hardware)
 - Transmission of audio and video signals
 - Supports HDR
 - Supports HDCP 1.4 and 2.2
 - USB Power Delivery (PD)
 - Slide switch for USB-C™ male
 - 1 x LED indicator
 - Metal housing
 - Colour: grey
 - Dimensions (LxWxH): ca. 125 x 35 x 12 mm
-

System requirements

- Android 8.0 or above
 - Chrome OS 76.0 or above
 - iPad Pro (2018)
 - Linux Kernel 4.3 or above
 - Mac OS 10.15.1 or above
 - Windows 7/7-64/8.1/8.1-64/10/10-64
 - MacBook Pro with two adjacent Thunderbolt™ 3 ports
 - Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3 port
-

Package content

- Docking station
- User manual

Images



Interface

Connector 1:	2 x USB Type-C™ male
Connector 2:	1 x HDMI-A female
Connector 3:	2 x USB 5 Gbps Type-A female
Connector 4:	1 x USB 5 Gbps USB Type-C™ female PD 2.0

Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 60 Hz
----------------------------	---------------------

Physical characteristics

Housing material:	metal
Colour:	grey

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de