

USB 2.0 Cable Type-A male to USB Type-C™ male angled with LED and Fast Charging 60 W 3 m

Description

This USB cable by Delock enables the connection between a device with a USB Type-C™ connector and a PC or a laptop equipped with a free USB port. Optically it convinces with its fine textile shielding and with its connectors in transparent housing.

Fast charging and power

The USB data and charging cable enables fast charging with its 60 W with a power bank or modern USB chargers. Quick Charge 3.0 is supported up to 20 V and 3 A.

LED indicator

As soon as the cable is connected to a power source, the LED lights up in green and then changes to a colour gradient with three different colours (green, orange, red), when a device is charged. The lighting is always discreet and inconspicuous.



3 m

Item no. 80768

EAN: 4043619807680

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A male
 - 1 x USB 2.0 USB Type-C™ male angled
- Cable gauge:
 - 28 AWG data line
 - 20 AWG power line
- Fast Charging function: 20 V / 3 A (60 W)
- Cable diameter: ca. 3.5 mm
- Data transfer rate up to 480 Mbps
- Cable with textile shielding
- Connector with metal housing and LED
- Colour: black / silver
- Length: ca. 3 m

Package content

- USB 2.0 cable

Images



General

Specification:	USB 2.0 USB Type-C™
----------------	------------------------

Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x USB 2.0 Type-C™ male

Technical characteristics

Data transfer rate:	480 Mbps
Maximum current:	3 A

Physical characteristics

Cable gauge:	28 AWG data line 20 AWG power line
Length:	3 m
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de