

Easy 45 Module USB 2.0 Retractable Cable USB Type-A to 8 Pin Lightning female white

Description

This Easy 45 retractable cable by Delock can be connected to a PC, laptop or power source with USB-A connector and can be used to transfer data or charge various devices with 8 Pin Lightning interface. The simple snap-in mechanism ensures that the module is firmly in place and can be easily removed if necessary.

Flexible

The USB 2.0 cable can be pulled out in six steps and thus offers different cable lengths, depending on requirements. If the cable is not needed, it is neatly rolled up and stowed away.

Easy 45 connects

Easy 45 is a variable, modular system that allows components such as sockets, HDMI or USB connections to be added according to your needs. The Easy 45 modules are standardised and can be mounted in various module holder or cable ducts. Easy 45 builds the interface between electrical, network and system installation and many peripheral devices such as TV, monitors, printers, laptops and much more.



Item no. 81331

EAN: 4043619813315

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
1 x USB 2.0 Type-A male
1 x 8 pin Lightning male
- Cable gauge:
Charging cable: 24 AWG
data cable: 30 AWG
- Flat cable
- Maximum output current: 2 A
- Data transfer rate up to 480 Mbps
- Voltage: max. 5 V
- Length incl. connectors:
USB-A Host-cable ca. 12 cm
Lightning device-cable ca. 50 cm (extended)
- Suitable for module holder Delock Easy 45

- Suitable for 45 mm cable duct with minimum depth 45 mm
- Module size: 22.5 x 45 mm
- Dimensions (LxWxH): ca. 45.0 x 22.5 x 47.0 mm
- Colour: white

System requirements

- Power source with a free USB Type-A port
- PC or laptop with a free USB Type-A port
- Device with 8 pin Lightning port
- A free module port Delock Easy 45

Package content

- Easy 45 module retractable cable

Images



General

Specification:	USB 2.0
----------------	---------

Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x Apple Lightning™ male

Technical characteristics

Data transfer rate:	480 Mbps
Maximum current:	2 A
Voltage:	5 V

Physical characteristics

Connector color:	white
Length:	47 mm
Width:	22.5 mm
Colour:	RAL 9003 Weiß

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

