

TC

XX

Number of contacts

X

Pitch

X

Screw&Clamp

X

Color

X

Tail length

X

X

X

X

X

End Stackable
02 2 contacts
03 3 contacts
.. ...
24 24 contacts
(pitch 5.0&5.08)
12 12 contacts
(pitch 10.0&10.16)

0 5.0/.197"
1 10.0/.394"
2 5.08/.20"
3 10.16/.40"

2 "+/-" Combination type
W/Brass Machined Clamp
3 "- " Slotted screw
W/Brass Machined Clamp

0 Black
5 Green
(RAL 6018/T)
6 Blue
8 Grey
(RAL 7035/D)
C Green
(RAL 6018/U)

0 4.4mm
1 3.8mm
2 3.5mm
3 2.9mm
(only pitch
5.0&10.0)

0000 2 Inter lock
(Steel screw plating Cr³⁺)
A500 Solid block
(Steel screw plating Cr³⁺)
(only pitch 5.0&10.0)
C500 Hi temp
(Steel screw plating Cr³⁺)
(only pitch 5.0&10.0)
Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy