

Product Datasheet

Item No.: 860560

as
Schwabe
TechnikProdukte

PRODUCT NAME

Solid rubber multi socket outlet S4, 2 m H07RN-F 5G2,5 11 kW "F"



- Housing made from extremely robust solid rubber
- Versions with various inputs and outputs for heavy-duty construction site use
- IP44: protected against foreign bodies and splash-proof

Reference image

Technical data

EAN	4059948004331
Weight [kg]	3.9
Dimensions	16x12x50 cm
Main color	black
Category	CEE 400 V product range
Subcategory	CEE multi socket outlets series S
Cable type	H07RN-F
Cross section [mm ²]	5G2,5
Cable color	black
Cable length [m]	2
Rated voltage [V]	400
Rated current [A]	16
Maximum power	11 kW
IP protection	IP44
Input	CEE plug 400 V, 16 A, 5-pole with 2 m H07RN-F 5G2,5
Output	3x shock-proof socket outlet 230 V, 16 A, IP44 "F" 2x CEE socket 400 V, 16 A, 5-pole
Total number of sockets	5
Number of Type E sockets (230 V)	3
Number of CEE 400 V 16 A sockets	2

Your partner for professional lighting and electrical products.