

TAH2535F2
ERGO™ Magnetic Pick-ups with Dyneema String

PRODUCT DETAILS

- Magnetic pick-up
- Three-component handle developed according to the scientific ERGO™ process
- Soft material with ridged surface provides superior grip and greater force transmission
- Flat face to prevent rolling
- Neodym magnet Ø10 mm, capacity 1 kg/35 oz
- Suitable for working at height
- Permanent Dyneema textile wire loop maintains user ergonomics and full functionality
- Colour plate with maximum weight for a right matching with the lanyard
- According to DROPS best practices

PRODUCT ATTRIBUTES

Product	∅				g
TAH2535F2	13 mm	405 mm	27x120 mm	522 mm	170 g

Follow the Fish!