

Adapter USB Type-C™ male > VGA female (DP Alt Mode) + USB Type-A + USB Type-C™ PD

Description

This adapter by Delock is suitable for the connection of a VGA monitor to a computer with USB-C™ interface and DisplayPort alternate mode support. Thus, the adapter can be connected to different laptops like MacBook, Chromebook and similar. In addition, the adapter can also be operated on a Thunderbolt™ 3 interface. Additionally the adapter has a USB 3.1 Type-A port and a USB-C™ port. The USB-C™ port can be used for power supply of the output device or to transfer data in USB 3.1 Gen 1 speed. Different USB devices such as docking stations, card reader, external enclosure etc. can be connected.



Item no. 62992

EAN: 4043619629923

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x SuperSpeed USB (USB 3.1 Gen 1) USB Type-C™ male >
 - 1 x VGA 15 pin female
 - 1 x SuperSpeed USB (USB 3.1 Gen 1) Type-A female
 - 1 x SuperSpeed USB (USB 3.1 Gen 1) USB Type-C™ Power Delivery female (optional for power supply)
- Chipset: VIA VL101 + VL813 + ITE IT6516
- DisplayPort 1.1a specification
- Resolution up to WUXGA 1920 x 1200 @ 60 Hz (depending on the system and the connected hardware)
- Transfer of analogue video signals
- USB bus powered
- Plug & Play
- Gold-plated connectors
- 1 x ferrite core
- Metal housing
- Cable length without connectors: ca. 20 cm
- Colour: grey

System requirements

- Windows 7/7-64/8.1/8.1-64/10/10-64, Mac ex OS 10.12.5
- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or
- PC or laptop with a free Thunderbolt™ 3 port

Package content

- USB-C™ to VGA Adapter + USB Type-A

Images



General

Function:	Plug & Play
Supported operating system:	Mac OS 10.12 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit

Interface

Output:	1 x VGA 15 pin female 1 x USB 5 Gbps Type-A female
Input:	1 x USB Type-C™ female (power supply) 1 x USB Type-C™ male

Technical characteristics

Maximum screen resolution:	1920 x 1200 @ 60 Hz
----------------------------	---------------------

Physical characteristics

Cable length:	20 cm
---------------	-------

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de