

## Product information

# 70 01 180

## Diagonal Cutter

DIN ISO 5749

- The indispensable diagonal cutter for all-round use
- High-quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting edge tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- With bevel
- Vanadium electric steel, forged, multi stage oil-hardened



### General

|             |                  |
|-------------|------------------|
| Article No. | 70 01 180        |
| EAN         | 4003773018070    |
| Pliers      | black anodized   |
| Head        | polished         |
| Handles     | plastic coated   |
| weight      | 200 g            |
| Dimensions  | 180 x 86 x 14 mm |
| Standard    | DIN ISO 5749     |

### Technische Attribute

|                                                |          |
|------------------------------------------------|----------|
| Cutting capacities medium hard wire (diameter) | Ø 3.0 mm |
| Cutting capacities hard wire (diameter)        | Ø 2.5 mm |
| Cutting capacities soft wire (diameter)        | Ø 4.0 mm |

### Classification

|                |            |
|----------------|------------|
| eCl@ss 5.1.4   | 21040302   |
| ETIM 5.0       | EC000165   |
| ETIM 6.0       | EC000165   |
| proficl@ss 6.0 | AAA949c004 |
| UNSPSC 13.1    | 27112114   |

technical change and errors excepted