

903E/C98

14" 12"

375x295x84mm - 6,0 kg

	art.	
009031098	903E/C98	C900: 14" 4-4,5-5-5,5-6-7-8-9-10-11-12-13-14 mm C900L: 14" 6-7-8-9-10-11-12-13 mm C900/25 14" C900/30 14" C900/42 14" C900/20: 14" 50 mm C900/20L: 14" 100 mm 900E/55 14" C900AD 10 14" C920A: 12" 10-11-12-13-14-15-16-17-18-19-20-21-22-24-27-30-32 mm C920L: 12" 14-15-17-19-22 mm C956C: 12" 16 mm - (5/8") - 21 mm (13/16") 920E/55 12" C920/25 12" C920/21: 12" 125 mm C920/22: 12" 250 mm C910/16F: 3/8" 1/2" 96: 1,3-1,5-2-2,5 mm C895/6: 5/16" 1/2" C900AD: 10 14" 892/0: 1/4" 1/4" 861PH: 10 1-2 861PZ: 10 1-2 861PE: 10 3-4-5-6 mm 861LP: 10 0,6x4-0,8x5,5-1,2x6,5 mm 861TX: 10 T10-T15-T20-T25-T27-T30 C866LP: 10 1,6x8-1,6x10-2,0x12 mm C866PH: 10 3-4 C866PZ: 10 3-4 866PE: 10 7-8-10-12-14 mm 866TX: 10 T40-T45-T50-T55-T60-T70

