

# USB 5 Gbps Hub with 7 USB Type-C™ Port with switch thereof 6 x Data Port + 1 x Data and PD 20 Watt

## Description

The USB hub by Delock can be connected via **USB Type-C™ interface** to a PC or laptop. It has **seven USB-C™ connectors**. Different USB devices such as USB flash memory, card reader, external enclosure etc. can be connected.

### USB-C™ PD 3.0 port

The USB Type-C™ PD port provides up to **20 watts of output power**. Connected devices such as smartphones can be charged or data can be transferred at 5 Gbps.

### Individual switch

Each port can be turned **on or off** individually by using the **switches**.

### Please Note

DisplayPort Alternate Mode (DP Alt Mode) is not supported, so no video signals are transmitted and no monitors can be connected.



**Item no. 63410**

EAN: 4043619634101

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x USB 5 Gbps USB Type-C™ male
  - 6 x USB 5 Gbps USB Type-C™ female
  - 1 x USB 5 Gbps USB Type-C™ female PD 3.0 (max. 9 V / 2.22 A)
  - 1 x 12 V DC jack
- Data transfer rate up to 5 Gbps
- Host device cannot be charged via PD port
- 7 x LED indicator
- 7 x switch
- Robust metal housing
- Electrical power per port: max. 5 watt (5 V / 1 A)
- Colour: midnight blue
- Plug & Play
- Cable length: ca. 60 cm
- Dimensions (LxWxH): ca. 139 x 50 x 17 mm

## Power supply specification

- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 0.8 A
- Output: 12.0 V / 3.0 A / 36.0 W
- Ground outside, plus inside
- Dimensions:
  - inside:  $\varnothing$  ca. 2.5 mm
  - outside:  $\varnothing$  ca. 5.5 mm
  - length: ca. 10 mm

---

## System requirements

- Android 11.0 or above
- Chrome OS
- Linux Kernel 6.2 or above
- Mac OS 13.1 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- Surface Pro 7
- Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 or Thunderbolt™ 4 port

---

## Package content

- Hub USB 5 Gbps
- External power supply
- User manual

---

## Images



## General

Function:	Plug & Play
Supported operating system:	Chrome OS Surface Pro 7 Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Android 11.0 or above Mac OS 13.1 or above Linux Kernel 6.2 or above
LED indicator:	7 x

## Interface

Connector 1:	1 x USB 5 Gbps USB Type-C™ male
Connector 2:	6 x USB 5 Gbps USB Type-C™ female
Connector 3:	1 x USB 5 Gbps USB Type-C™ female PD 3.0 (max. 9 V / 2.22 A)
Connector 4:	1 x 12 V DC jack

## Technical characteristics

Data transfer rate:	5 Gbps
---------------------	--------

## Physical characteristics

Housing material:	metal
Cable length:	60 cm
Length:	139 mm
Width:	50 mm
Height:	17 mm
Colour:	midnight blue

## Manufacturer information

---

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de