

Easy 45 Module SuperSpeed USB 10 Gbps (USB 3.2 Gen 2) USB Type-A female to USB Type-C™ male with pigtail, 22,5 x 45 mm

Description

This Easy 45 module by Delock is designed to provide a USB Type-A female port. The simple snap-in mechanism ensures that the cover is firmly in place and can be easily and toolless changed if necessary.

Easy 45 connects

Easy 45 is a variable, modular system that allows components such as sockets, HDMI or USB connections to be added according to your needs. The Easy 45 modules are standardised and can be mounted in various module holder or cable ducts. Easy 45 builds the interface between electrical, network and system installation and many peripheral devices such as TV, monitors, printers, laptops and much more.



Item no. 81388

EAN: 4043619813889

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x SuperSpeed USB 10 Gbps (USB 3.2 Gen 2) USB Type-C™ male >
 - 1 x SuperSpeed USB 10 Gbps (USB 3.2 Gen 2) Type-A female
- Host = USB Type-C™; Device = USB Type-A
- Cable gauge:
 - 30 AWG data line
 - 22 AWG power line
- Output current: up to 3 A
- Cable diameter: ca. 4.5 mm
- Data transfer rate up to SuperSpeed USB 10 Gbps
- Length incl. connectors: ca. 1 m
- Material: PC plastic
- Suitable for module holder Delock Easy 45
- Suitable for 45 mm cable duct with minimum depth 45 mm
- Module size: 22.5 x 45 mm
- Dimensions (LxWxH): ca. 22.5 x 45.0 x 38.5 mm
- Colour: white

System requirements

- A free module port Delock Easy 45

Package content

- Easy 45 module

Images



General

Mounting type:	Easy 45
Specification:	USB 10 Gbps

Interface

Connector:	1 x USB Type-A female
Connector 1:	1 x USB Type-C™ male

Physical characteristics

Connector color:	black
Housing material:	Plastic
Length:	27.6 mm
Width:	22.5 mm
Height:	45 mm
Colour:	RAL 9003 Weiß

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

