USB Type-C™ Docking Station 4K - HDMI / USB Hub / PD 3.1 140 W

Description

This docking station by Delock can be connected to a computer with a USB-C™ DP Alt Mode or Thunderbolt™ 3, Thunderbolt™ 4 or Thunderbolt™ 5 port and provides a variety of interfaces. A monitor can be operated at the **HDMI output** port by a maximum resolution up to **4K**. **Two built-in USB Type-A** and **one USB-C™** port allow the use of peripherals.



USB Power Delivery (USB PD 3.1) support up to 140 watt

The docking station has a **USB Type-C™ Power Delivery port**. If this port is connected to the power supply of the laptop or tablet, the host device is charged with up to **125 watts** during operation.

Item no. 92003

EAN: 4043619920037

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
  1 x USB 10 Gbps USB Type-C™ male
  1 x HDMI female
  1 x USB 10 Gbps USB Type-C™ female
  1 x USB 10 Gbps Type-A female
  1 x USB 2.0 Type-A female
  1 x USB Type-C™ PD female (power supply)
- Resolution up to 3840 x 2160 @ 60 Hz (depending on the system and the connected hardware)
- Transmission of audio and video signals
- Supports HDCP 1.4 and 2.3
- Supports HDR
- Input power PD port: 140 W, 15 W are used for the docking station
- Output power for host: max. 125 W
- Metal housing
- Cable length without connectors: ca. 20 cm
- Colour: grey
- Dimensions (LxWxH): ca. 128 x 34 x 11 mm

System requirements

- Android 15.0 or above

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

- Chrome OS
- Linux Kernel 6.14 or above
- Mac OS 15.6.1 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- iPhone 15 Pro or above
- Surface Pro 9
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3, Thunderbolt™ 4 or Thunderbolt™ 5 port

Package content

- USB-C™ docking station
- User manual

Images







All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

General

Supported operating system:	Chrome OS Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 iPhone 15 Pro or above Surface Pro 9 Android 15.0 or above Linux Kernel 6.14 or above Mac OS 15.6.1 or above

Interface

Connector:	1 x USB 2.0 Type-A female 1 x USB 10 Gbps USB Type-C™ male 1 x USB 10 Gbps Type-A female 1 x USB 10 Gbps USB Type-C™ female 1 x HDMI female 1 x USB Type-C™ PD female (power supply)

Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 60 Hz

Physical characteristics

Cable length:	20 cm
Material:	metal
Length:	128 mm
Width:	34 mm

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Height:	11 m
Colour:	grey

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**