



Technical sheet

No.

11FA07A

Issue

V01.0

Product family: Cable-ties - Nylon cable-ties
Item code: BP1536, BP2048
Description: NYLON CABLE-TIES · PUSH MOUNT

Image



Specifications

MATERIAL: polyamide (PA 6.6)
COLOR: natural
INSULATION SELF-EXTINGUISHING: UL 94 V2
OPERATING TEMPERATURE: from -40 °C to +85 °C
MINIMUM INSTALLATION TEMPERATURE: -10 °C
CHEMICAL RESISTANCE: good resistance to bases, oils, grease, chloride solvents. Limited resistance to acids. Not resistant to phenols.
ACCORDING TO STD.: EN 62275:2015-02
CLASSIFICATION: type 1 (EN), type 21 (UL)
ASSEMBLY: open the package just before use

Code	Width (mm)	Length (mm)	Fixing hole Ø (mm)	Max bundle Ø (mm)	Min bundle Ø (mm)	Tensile minimum resistance (N)	
BP1536	3,6	155	6	37,9	3,5	180	100/2500
BP2048*	4,8	200	8	50,8	3,5	230	100/1500



* file n° E 223175

**HALOGEN
FREE**