

VK15C562
CONNECTION TECHNOLOGY • CABLE SOCKETS / CONNECTORS PRE-ASSEMBLED ON TWO SIDES

, 1.5m, Valve connector type B Female (socket) 3pin Angular, M12
Male (plug) 5pin Straight, 3x0.5mm², PUR (Polyurethane), With LED display


MECHANICAL FEATURES

Cable infeed of A connection	Angular
Cable infeed of B connection	Straight
Cable length	1.5 m
Material of cable sheath	PUR (Polyurethane)
Number of cores	3
Version	Connection cable
Wire cross section	0.5 mm ²

ELECTRICAL FEATURES

Number of pins of A connection	3
Number of pins of B connection	5
Type of A electrical connection	Valve connector type B
Type of B electrical connection	M12
Type of plug-in contact, A connection	Female (socket)
Type of plug-in contact, B connection	Male (plug)
With LED display	+

OTHER FEATURES

IR-networked	-
--------------	---

Other

Packaging dimensions	160mm x 20mm x 235.0mm
Shipping weight	0.08kg
Tariff code	85444290

Classification

ipf product group	700
eClass 8.0	27279218
eClass 9.0	27060311
eClass 9.1	27060311
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855

Connection**Dimensional drawing****Installation**

Mounting / installation may only be carried out by a qualified electrician!

Disposal**Safety warnings**

Before initial operation, please make sure to follow all safety instructions that may be provided in the product information.

Never use these devices in applications where the safety of a person depends on their functionality.

LED lighting systems can generate intensive UV radiation, which can damage your eyes in case of improper use. The manufacturer cannot be held responsible for damages that result from improper use or connection.