



BETA 7275N FitEVOLUTION microfibre shoe, water-repellent



Certifications and Standards



S3S FO SR ESD

EN ISO 20345:2022

Features

The 7275N is the perfect synthesis of durability and functionality: BETA orange outsole and details enhance the robust black microfibre upper.

FIT4YOU system

Create your own comfort with BETA's patented FIT4YOU system: a special cavity in the penetration proof insole allows you to replace the ETPU insole at any time, choosing from three different densities included in the pack.

ETPU inserts

ETPU is known for its excellent anti-shock and shock-absorbing properties. The three inserts soft, intermediate and rigid make it easy and immediate to customise the softness and support of the shoe to suit your needs.

All-season durability

The water-repellent microfibre upper is incredibly resistant to stains and scratches, perfect for all-season use. It is ideal for shoes built to last, without compromising on quality.

Metal-free

Composite toe cap and midsole are made of composite material to provide lightweight, metal-free protection.



FIT4YOU

The patented FIT4YOU technology, with the 3 ETPU inserts included in the pack, allows the shoe's cushioning to be personalised



Customised comfort

The special pressed sheet allows you to create your own comfort by choosing from 3 different ETPU inserts included in the pack.



ESD protection

ESD certified to protect user and machinery from electrostatic charges



Certifications and Standards



S3S FO SR ESD

EN ISO 20345:2022



Specifications

LACING:	traditional
WEIGHT (INDICATIVE SIZE 42):	590 g
TYPE:	low

Lightness

- Water-repellent microfibre
- Heel stability support
- Traditional lacing

Comfort

Dual-density polyurethane

Safety

3-density cushioning ETPU insert and EVA FOAM underfoot cover

Protections

Tip: Polymer material, 200 joules.

Durability: Composite fibre, ceramic treatment.

Coded items

	Art.	EU	UK	 mm
072750237	7275N 37	37	4,5	251
072750238	7275N 38	38	5	257
072750239	7275N 39	39	6	263
072750240	7275N 40	40	6,5	269
072750241	7275N 41	41	7	276
072750242	7275N 42	42	8	282
072750243	7275N 43	43	9	290
072750244	7275N 44	44	10	296
072750245	7275N 45	45	10,5	304
072750246	7275N 46	46	11	311
072750247	7275N 47	47	12	317
072750248	7275N 48	48	13	324

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

