

RJ45 Network Cable with braided coating Cat.6A U/FTP Slim 1 m blue

Description

This network cable by Delock can be used to connect different networking devices, e.g. a NIC to a switch or a patch panel.

Slim patch cable

The thin patch cables are characterised by their small cable diameter and enable flexible and space-saving cabling in the network cabinet.

With braided jacket

The jacket provides excellent resistance to abrasion and protects the network cable from kinks and breaks. Thus, the cable remains durable.



Item no. 80377

EAN: 4043619803774

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x RJ45 plug
 - 1 x RJ45 plug
- Cat.6A specification
- Data transfer rate up to 10 Gbps
- Bandwidth: 500 MHz
- Shielded (U/FTP)
- Slim
- With braided jacket
- Cable gauge: 32 AWG
- Contacts gold-plated: 50 µ"
- Cable diameter: ca. 4.1 mm
- Cable jacket material: nylon braid
- Colour: blue
- Length: ca. 1 m

System requirements

- A free RJ45 jack

Package content

- RJ45 cable

Images



General

Specification:	Cat. 6A
Style:	both sides identical

Interface

Connector 1:	1 x RJ45 male
Connector 2:	1 x RJ45 male

Physical characteristics

Cable gauge:	32 AWG
Material:	Nylon braid
Shielding:	U/FTP
Length:	1 m
Colour:	blue

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de