

Delock Antenna Base SMA plug > SMA Jack LTE MIMO 1 m black low loss

Description

This practical antenna base can be used universally in following applications:

1. upright on the table
2. hanging on the wall

Use it to position the antennas for best performance.



1 m

Item no. 88739

EAN: 4043619887392

Country of origin: Taiwan,
Republic of China

Package: Zip poly bag

Technical details

- Connector:
Antenna: 2 x SMA jack
Cable: 2 x SMA plug
- Cable length: 1 m
- Cable type: ULA100 low loss
- Cable attenuation:
1,40 dB @ 2.5 GHz
2,30 dB @ 5.8 GHz
- Operating temperature: -10 °C ~ 55 °C
- ABS UV resistant

Package content

- Antenna base LTE MIMO

Images



Interface

Connector 1:	2 x SMA jack
Connector 2:	2 x SMA plug

Technical characteristics

Operating temperature:	-10 °C ~ 55 °C
------------------------	----------------

Physical characteristics

Housing material:	ABS UV resistant
Cable type:	ULA 100 low loss
Cable attenuation:	1.4 dB @ 2.500 GHz pro Meter 2.3 dB @ 5.8 GHz per meter
Cable length:	1 m

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

