

Panel Mount Push-button black

Description

This panel mount by Delock works as an On/Off switch or reset button for electronic components and can be installed in e.g. a housing or device.



Item no. 91187

EAN: 4043619911875

Country of origin: China

Package: Zip poly bag

Technical details

- Connector: 2 x solder connection
- Operating voltage / current: max. 24 V / 1 A
- Integrated name plate
- Panel cut-out (WxH): ca. 16.8 x 22.3 mm
- Countersink for conical screws, distance ca. 28.9 mm
- Mounting hole diameter: ca. 3.3 mm
- Screw type: #4-40 UNC
- Material: zinc diecast / plastic
- Colour: black
- Dimensions (LxWxH): 19.8 x 19.1 x 35.5 mm

Package content

- Panel Mount

Interface

Connector:	1 x 2 soldering pin
------------	---------------------

Technical characteristics

Operating voltage:	24 V / 1 A
--------------------	------------

Physical characteristics

Material:	zinc diecast / plastic
Length:	19.8 mm
Width:	19.1 mm
Height:	35.5 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

