

USB 20 Gbps USB-C™ Memory Stick 256 GB, Read Speed: 1980 MB/s - Metal Housing

Description

This USB memory stick by Delock can be used to save and transport data, e.g. photos, videos or music. Thanks to the **USB Type-C™ connector**, the stick can be quickly and easily connected to various devices such as laptop, PC, smartphone, tablet or Smart TV.

Small, stable and handy

Due to its **small dimensions and its sturdy housing**, this Delock USB stick is particularly suitable for travelling. Due to its tiny size, the USB stick fits into any trouser pocket.



Item no. 54012

EAN: 4043619540129

Country of origin: China

Package: Retail Box

Technical details

- Connector: 1 x USB 20 Gbps USB Type-C™ male
- Capacity: 256 GB
- Housing material: metal
- Maximum read speed: 1980 MB/s
- Operating temperature: 0 °C ~ 70 °C
- Storage temperature: -40 °C ~ 85 °C
- Power consumption: max. 2.75 W
- Field of application: consumer
- Bootable
- Plug & Play
- Weight: ca. 34 g
- Dimensions (LxWxH): ca. 69 x 20 x 9 mm

Package content

- USB-C™ memory stick
- Silicone case

Images



Interface

Connector:	1 x USB 20 Gbps USB Type-C™ male
------------	----------------------------------

Technical characteristics

Storage temperature:	-40 °C ~ 85 °C
Operating temperature:	0 °C ~ 70 °C
Read:	1980 MB/s
Maximum power consumption:	2.75 W
Memory capacity:	256 GB

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de