

WiFi 2.4 GHz Antenna BNC plug 2 dBi 14.5 cm omnidirectional with tilt joint black

Description

This WLAN antenna by Delock allows the usage of different WLAN bands inside.



Item no. 90737

EAN: 4043619907373

Country of origin: Taiwan,
Republic of China

Package: White Box

Technical details

- Connector: 1 x BNC male
- Frequency range:
2.400 - 2.500 GHz
- Antenna gain: 2 dBi
- Impedance: 50 Ohm
- VSWR: 2.0
- Polarisation: vertical
- HBW horizontal beamwidth: 360°
- VBW vertical beamwidth: 70° - 80°
- Transmission power: max. 2 W
- Operating temperature: -10 °C ~ 55 °C
- Housing material: ABS
- Colour: black
- Weight: ca. 41 g
- Dimensions (LxD): ca. 114.5 x 14.5 mm

System requirements

- Device with one free BNC port

Package content

- Antenna

General

Suitable for indoor:	yes
----------------------	-----

Interface

Connector:	1 x BNC male
------------	--------------

Technical characteristics

Frequency range:	2400 - 2500 MHz
Antenna gain:	2 dBi
Beam width horizontal:	360°
Beam width vertical:	70° - 80°
Impedance:	50 Ω
Operating temperature:	-10 °C ~ 55 °C
Polarisation:	vertical
Transmission power:	2 W
VSWR:	2.0

Physical characteristics

Colour:	black
Dimensions (LxD):	114.5 x 14.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

