

In-Desk Hub 3 Port USB 3.0 + 2 Slot SD Card Reader

Description

This hub by Delock can be installed into an existing cut-out of the desk with a diameter of 60 mm or 80 mm to lead through the cables for the monitor, keyboard and mouse. At the same time, the hub offers three USB Type-A female ports and one SD Card Reader with two slots. The data transfer and power supply is guaranteed through one USB 3.0 Type-A male and one USB 2.0 Type-A male. The distance between the free connectors can be maximum 20 cm, because the two cables are connected with each other.



Item no. 62869

EAN: 4043619628698

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - top side:
 - 3 x USB 3.0 Type-A female
 - 1 x SD slot
 - 1 x Micro SD slot
 - bottom side:
 - 1 x USB 3.0 Type-A male
 - 1 x USB 2.0 Type-A male (power supply)
- Chipset: VL813, GL3233
- Data transfer rate up to:
 - SuperSpeed USB 5 Gbps,
 - Hi-Speed 480 Mbps,
 - Full-Speed 12 Mbps,
 - Low-Speed 1.5 Mbps
- The Card Reader supports following memory cards:
 - 1. Slot Secure Digital**
 - SD, SD Pro, SD High Capacity (SDHC), SD Ultra, SDHC Ultra, SDXC, SDXC Ultra,
 - MMC-I, MMC-II, MMC 4.0, Mini SD, Mini SDHC, MMCmobile, RS-MMC, RS-MMC 4.0
 - 2. Slot Micro Secure Digital**
 - Micro SD, Micro SDHC, Micro SDHC Ultra, T-Flash, MMCmicro
- Mounting diameter: 60 mm / 80 mm
- Mounting depth: 35 mm
- Cable length: ca. 95 cm
- Plug & Play

System requirements

- Linux Kernel 2.6 or above
- Mac OS 10.9 or above
- Windows 7/7-64/8.1/8.1-64/10/10-64
- PC or laptop with two free USB Type-A ports
- 60 mm product and 80 mm cut-out of the desk

Package content

- In-Desk Hub with Card Reader
- 60 mm ring
- 80 mm ring
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Linux Kernel 2.6 or above Mac OS 10.9 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit
Supported memory card:	Micro SD Micro SDHC Micro SDXC SD SDHC SDXC T-Flash MMCmicro miniSD MMC RS-MMC MMC-I MMC-II MMC 4.0 MMCmobile RS-MMC 4.0

Interface

Top side:	1 x SD slot 1 x Micro SD Slot 3 x USB 5 Gbps Type-A female
Bottom side:	1 x USB 5 Gbps Type-A male 1 x USB 2.0 Type-A male (power supply)

Technical characteristics

Chipset:	VIA VL813 Genesys Logic GL3233
----------	-----------------------------------



Data transfer rate:

5 Gbps

Physical characteristics

Cable length:	95 cm
Depth:	35 mm
Diameter:	80 mm 60 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

