

MA-DA2U-01

Adjustable desk 2-display mounting arm with USB ports, 17"-32"

- Position your screen perfectly
- Lightweight and full-motion design
- Practical integrated USB ports in the base



Features

- Monitor desk mount with double monitor arm and integrated USB ports
- Arms rotate, extend and retract, tilt to change reading angles, and allow to rotate display from landscape-to-portrait mode, etc
- Enables easy ergonomic positioning for reduced strain
- Practical integrated USB-ports for charging or data
- Works with almost any LCD monitor (max. 32")
- Durable adjustable gas-spring suitable for monitors up to 9 kg
- Built-in cable management for an organized and neat workspace

Packaging

Q'ty in crtn, pcs	4
Crtn volume, CUM	0.0302445
Crtn weight, kgs	18.55
Individual package size LxWxH:	384x108x160 mm
Carton size LxWxH:	390x330x235 mm
Country of origin	CN
Barcode	8716309135368
Customs code	8302500000

Package contents

Desk arm
User manual
Mounting tools bag

Certificates



Specifications

Material: Steel, plastic
Surface finish: Electrophoresis, Powder Coating
Color: fine texture black
USB interface: USB 3.2 Gen 1 (5 Gbps)
USB ports: 1x USB-C 1x USB-A
Supported screen size: 17" 32"
Weight capacity (per screen): 2 ~ 9 kg
VESA compatible: 75x75, 100x100 mm
Tilt range: +90° -90°
Swivel range: +90° ~ -90°
Screen rotation: +180° ~ -180°
Installation: grommet, clamp
Suggested desktop thickness: clamp: 10 ~ 80 mm, grommet: 10 ~ 48 mm

Cable management: yes