

Delock Cable FireWire A to pinheader

Description



16 cm

Item no. 82379

EAN: 4043619823796

Country of origin: China

Package: Zip poly bag

Technical details

Interface

Connector 1:	1 x FireWire 1394A 6 pin plug
Connector 2:	1 x 10 pin USB 2.0 pin header male

Technical characteristics

Data transfer rate:	400 Mbps
---------------------	----------

Physical characteristics

Cable gauge:	28 AWG data line 24 AWG power line
Length:	16.5 cm
Colour:	black
Cable diameter:	6 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

