

## Product information

# 98 25 01 SL

## Screwdriver (Slim) for cross-recessed screws

Pozidriv®

IEC 60900 DIN EN 60900

- Reduced blade isolation diameter for recessed spring and screw elements
- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel



⚡ 1000V ⚡

### Allgemein

|             |                                               |
|-------------|-----------------------------------------------|
| Article No. | 98 25 01 SL                                   |
| EAN         | 4003773079774                                 |
| point       | burnished                                     |
| Handles     | insulating multi-component handle, VDE-tested |
| weight      | 61 g                                          |
| Dimensions  | 187 x 87 x 30 mm                              |
| Standard    | DIN EN 60900 IEC 60900                        |

### Technische Attribute

|                               |        |
|-------------------------------|--------|
| Size                          | PZ1    |
| Blade length                  | 80 mm  |
| Handle length                 | 107 mm |
| Length of non-insulated blade | 15 mm  |
| VDE tested                    | yes    |

### Classification

|                |            |
|----------------|------------|
| eCl@ss 5.1.4   | 21040401   |
| ETIM 5.0       | EC000144   |
| ETIM 6.0       | EC000144   |
| proficl@ss 6.0 | AAA818c006 |
| UNSPSC 13.1    | 27111701   |

*technical change and errors excepted*

*Pozidriv® is a registered trademark of European Ind. Serv. Ltd.*